

This content has been provided by www.webpackaging.com



In-house metallization process by Virospack

Virospack continually aims to improve the services available to customers therefore they decided to create a new internal metalizing section that can now metalize plastic caps and glass vials up to 10ml.

For drying methods they have two options- the traditional heating chamber can be used or ultraviolet drying is available. The presence of two door vacuum chambers in the line will allow the management of high capacity orders.

The biggest advantage is that all the orders can be delivered within a short lead time whilst respecting customer's quality requirements thanks to the increase of their in-house decorating facilities.

Virospack also offers other in-house decoration processes such as:

Water based electrostatic painting
Aerographic painting – for lacquered, gradient or 2 coat paints



[Click here to visit this online at WEBpackaging](http://www.webpackaging.com)