

# GLASEL

GLASEL MAIL NEWS vol.0191



A bottle family whose shape transforms from a round cross section at the shoulder to square at the bottom, to give a stylish yet soothing impression.

## IBE

LOTION • ATOMIZER • DROPPER



Information  
IBE-120H  
will be launched  
within days.

IBE-50A

IBE-80A

IBE-100H

IBE-150H

IBE-200H

Various image decorations

The IBE family coordinates well with the newly released double caps IBL-120W DOUBLE and JWL-24L, as well as with WKAT-44.2 CAP.



IBL-120W DOUBLE  
(Inner cap: PP Outer cap: AS)



JWL-24L  
(Inner cap: PP Outer cap: AS)



WKAT-44.2CAP  
(Inner cap: PP Outer cap: AS)

Product name	Capacity[mL] Full Volume O.F	Bottle size(mm)			Foming Method	Material	Compatible caps / accessories			
		H	W1	W2			CAP	STOPPER	DISPENSER	
<b>NEW</b> IBE-50A	61	95.5	36.5	27.1□	Injection stretch blow molding	PET	PHR-20 flip top cap G-200SP	/	Z-200-C036 Z-200-C035 Z-200-C024 Z-200-C093 Z-200-C159 Z-200-C160 MS180-24(Metal covering) GMS20-180	
<b>NEW</b> IBE-80A	91	114	40	29.5□						
<b>NEW</b> IBE-100H	115	123	42	30.5□			IBR-150CAP IBR-200CAP IBL-150CAP IBL-200CAP <b>NEW</b> IBL-120W DOUBLE WKAT-44.2CAP <b>NEW</b> JWL-24L KAT-24L, AY-24L BTA-24L, DM-24L		TB-24-3Φ TB-24-5Φ TB-24-8Φ	Z-500-C001 Z-500-C009 Z-500-C163 Z-650-1738 Z-650-1739 Z-500-C041 Z-500-C033 Z-500-C057 Z-500-C151 Z-155-C110 Z-305-C167
IBE-150H	168	144.5	46.5	33.5□						
<b>NEW</b> IBE-200H	219	156.5	51	36.6□			TON		TONII Stopper TONIII Stopper	

- Numbers in item names serve as a guide for the amount you can fill. Please check the actual articles by conducting tests such as filling and resistance to the contents.
- The capacity and bottle size figures are standard values (before decoration and in standard color), which may differ from measurements.
- Please note that the specifications are subject to change.

- For more details on caps and accessories, see the end of Standard catalog 2017 and Extra issue 2018.
- Caps and accessories are shown for example purposes only. Some specific bottles or sizes may not be nicely coordinated with some caps and accessories, even though they fit together. Please check the actual articles, or contact us.

\*Compatible only with the IBE-50A.

The content of this email newsletter may not be reproduced in any form without GLASEL's permission.