



Primary Packaging for Moisture Sensitive Solid Formulations



TE Cap with integrated desiccant capsule

Cleanroom fully automated production with moisture control

Range of HDPE bottles manufactured with Injection Blow Molding (IBM) technology

Tamper-Evident Cap with integrated desiccant capsule (0,5 - 3,0 g silica gel)

Tamper evident caps available with multilayer liner options – Foam, PS or Inductive Welding

Site working under GMP principles and ISO 15378:2011 and ISO 9001:2008 certified company

Raw Materials according the European Pharmacopoeia or Food Contact Legislation

Produced and automatically sealed under class 10.000 (ISO 7) cleanroom

Statistical Process Control (SPC) and Batch Quality Control (Vision Measuring Machine)

DMF type III (FDA) submission will be available soon

						
90100*	Bottle	20	HDPE	47~	40	36
90101		35		55	45	
90102*		50		64	46	
90149*		100		79	55	
90105	Cap Desic	n.a.	PP	23,5	42	
90120	Cap Liner	n.a.	PP	23,5	42	

*under development
Subject to changes

Progressoplaste, Lda.

Estrada de Polima nº 729 – Abóboda
2785-543 São Domingos de Rana
Cascais - PORTUGAL

Tel. + 351 214 454 289
Fax. + 351 214 452 448
Email. sales@plasticprogress.com
Web. www.plasticprogress.com

