


EXTRUSION BLOW MOLDING AIRLESS BOTTLES

www.srpackaging.com





The lighter, reliable, and cost-competitive extrusion blow molding (EBM) Airless Bottle requires no assembly and uses 70% less plastic than the piston type.


It broadens the applications from Beauty Care to Hair Care, Household Care, and beyond. From 15 ml to 250 ml, it gives options to formulate products without preservatives or additives,

EBM airless handles products of various viscosities, an opportunity to transform commodities into organic, clean beauty.



EBM AIRLESS
Looks like an
atmospheric pump.
Dispenses as an
airless.

www.srpackaging.com



The conventional piston type airless bottle has multiple parts that require assembly and is costly, narrowing business possibilities to solely prestige projects.



Airless Differences



airless, piston type

Multiple components: bottle plug, bottle piston, and bottle.

The high failure rate of drop tests due to malfunction and piston damage.

Complex component structure consumes more plastics.

Piston movement with possible mechanical failure that compromises product quality.

Protected by single-layered plastic of average packaging protection.



mechanism



Impact resistance



plastic usage



quality



chemical resistance



EBM Airless

The double-walled bottle design of a thin film inner layer pouch with the outer wall.

Impact-resistant 2-layer structure sustains drop test from 1 meter height.

Reduces 70% plastic usage.

Vacuum sealed inner pouch protects product and ensures less product residue.

EVOH+PP inner pouch, offers excellent chemical resistance and gas barrier.



Customizable Bottle Shape



Chemical Resistant



Less Product Residue

Recyclability



Mono-material EBM Airless Bottles

The lighter, more reliable, and cost-competitive EBM Airless Bottle has an airless PP pouch (with a less than 2% EVOH barrier) inside the rigid PP exterior wall.

It conforms to US and European packaging design regulations, entirely recyclable without disassembling.

Designed and made in Taiwan, EBM Airless Bottles are available with post-consumer recycled plastics provided by local recyclers that conform to EuCertPlast and European RoHS requirements.



(For the PP pump, the spring remains metal for reliable performance.)

Extrusion blow molding bottles (EBM Airless Bottles) can be airless or atmospheric.

Both are chemically compatible and impact-resistant, with a wide range of possible geometries and decoration options.

V.S

EBM Airless Bottle

ACI-180B sprayer / CHS7081B pump

2-layered bottle with a thin airless pouch

- ★ Airless
- Bottle weight 23 g
- OFC 186 ml
- ★ Available in PCR
- ★ No dip tube, upside-down usage
- ★ Extend shelf life
- ★ Preservative-free



EBM Bottle

BCA-160B + sprayer / pump / screw caps

single layered

- Not Airless
- ★ Bottle weight 19 g
- OFC 186 ml
- ★ Available in PCR
- With dip tube
- Average shelf life
- Preservative required




Transform your lineup with natural and botanical ingredients without fear of air degradation

Botanical and vegan, free of preservatives, the clean beauty trends require sustainable and efficient packaging for best protection, and EBM Airless Bottles are the answer.

EBM Airless Sprayers




- ✓ Rinse-free Shampoo Spray
- ✓ Natural Refreshing Mist
- ✓ Mineral SPF 50 Sun Mist
- ✓ Essential Oil Body Spray Moisturizer
- ✓ Herbal Deodorant Spray



EBM Airless Pumps

- ✓ Organic Shampoo
- ✓ Plant-based Body Wash
- ✓ Reef-safe Sunscreen Cream
- ✓ Waterless hydrating Balm
- ✓ Botanical Cream Deodorant

EBM (extrusion blow molding) Airless material options



PCR Airless opt for PCR PE & PCR PP for material option.


Protect Marine Life opt for recycled PE made of post-use fish nets and fishing gears.



Ref.	ACF-030	ACF-050	ACF-100	APA-050	ASA-078	APB-060	ACB-075	ACA-072	AOB-030	CHS7081B	ACI-180B	ASC-180B	ACB-180B	ACA-180B
OFC	36.7 ml	54 ml	105.5 ml	54.5 ml	82 ml	64.6 ml	77.5 ml	75.6 ml	35 ml	186.3 ml	186.7 ml	195 ml	195 ml	194 ml
DIM mm	H. 75.5 Ø 29	H. 106 Ø 29	H. 105 Ø 41	H. 83 L. 30.5 W. 30.5	H. 89.9 L. 34.2 W. 34.2	H. 94.74 Ø 33.54	H. 100 Ø 35.5	H. 111.1 Ø 33.1	H. 120 cap incl. L. 36.9 W. 20.8	H. 124.7 Ø 50.5	H. 127.3 Ø 50.5	H. 158 L. 41 W. 41	H. 129 Ø 50	H. 125 Ø 50
neck size	20	20	24	20	20	20	20	20	Special thread	24/410	24/410	24/410	24/410	24/410
Wt.	9 g	12 g	19 g	11 g	13 g	12.5 g	13.5 g	15 g	8.5 g	22.5 g	23 g	23.5 g	21.6 g	22.5 g

▶ Refillable EBM Airless bottles

PCR airless cartridges



ASB SERIES

Ref.	H. (mm)	L. / W. (mm)	Match pack	Dosage
ASB-015	100	38x38	ACE-015B	0.23 ml
ASB-030	129.7	38x38	ACE-030B	0.23 ml
ASB-050	149.7	38x38	ACE-050B	0.23 ml

ACH SERIES

Ref.	H. (mm)	L. / W. (mm)	Match pack	Dosage
ACH-015	100.1	Φ39.9	ACE-015B	0.23 ml
ACH-030	130	Φ39.9	ACE-030B	0.23 ml
ACH-050	147	Φ39.9	ACE-050B	0.23 ml

ACG SERIES

Ref.	H. (mm)	L. / W. (mm)	Match pack	Dosage
ACG-015	101.2	Φ43.5	ACE-015B	0.23 ml
ACG-030	130	Φ48.5	ACE-030B	0.23 ml
ACG-050	154	Φ48.5	ACE-050B	0.23 ml

ACE-B SERIES

Ref.	OFC(ml)	H. (mm)	L. / W. (mm)	Wt
ACE-015B	21.7	60	Φ27	5.7g
ACE-030B	35.9	89	Φ27	7.9g
ACE-050B	55.3	113	Φ29	10.5g

ACD SERIES

Ref.	H. (mm)	L. / W. (mm)	Match pack	Dosage
ACD-070	118.8 (Cap)	Φ48.6	ACD-070B	1.0 ml
ACD-105	145.8 (Cap)	Φ48.6	ACD-105B	1.0 ml
ACD-150	183.1 (Cap)	Φ48.6	ACD-150B	1.0 ml

ACD-B SERIES

Ref.	OFC(ml)	H. (mm)	L. / W. (mm)	Wt
ACD-070B	81	79.9	Φ41.5	12.2g
ACD-105B	114	106.9	Φ41.5	15.5g
ACD-150B	161	143.6	Φ41.5	25g

► Airless Shuttles

2-in-1, 3-in-1, 4-in-1
ultra-personalized beauty

| Airless Shuttle

Cap:PETG/Collar: PP
Case: PMMA



Cap:PETG/Collar: PP
Case: PMMA



Cap/Case: PET
Collar:ABS



AIRLESS SHUTTLE

Ref.	H. (mm)	L. / W. (mm)	Wt
CCA-060	116.2 (Cap)	Φ55.92	79g (Cap)
CCB-060	116.2 (Cap)	Φ55.92	79g (Cap)
CCC-060	110 (Cap)	Φ50.09	46.38g (Cap)

CCA-020-1 1/3 SPRAYER / CCA-020 1/3 PUMP

Ref.	OFC (ml)	H. (mm)	L. / W. (mm)	Match pack	Dosage	Wt
CCA-020-1	23.5	106.2	37.52	CCA-060	0.2 ml	15.1g
CCA-020	23.5	106.2	37.52	CCA-060	0.2 ml	15.1g

CCB-015 1/4 PUMP

Ref.	OFC (ml)	H. (mm)	L. / W. (mm)	Match pack	Dosage	Wt
CCB-015	18	106.09	29.91	CCB-060	0.2 ml	11.1g

CCC-030B 1/2 PUMP

Ref.	OFC (ml)	H. (mm)	L. / W. (mm)	Match pack	Dosage	Wt
CCC-030B	34	104.39	45.09	CCC-060	0.2 ml	17.4g

► RePod:

Refillable Airless Jar



Pump / Cap / Collar: PP
Case: PET

Cap: 3075AG



Ref.	OFC (ml)	H. (mm)	L. / W. (mm)	Dosage	Wt
CHS3075	58	84 (Cap)	Φ68	0.2 ml	107.5g(Cap)

► AMARI:

Twist-lock Airless Bottle



Pump : PP
Case: PET

Cap: 3075AG



Ref.	OFC (ml)	H. (mm)	L. / W. (mm)	Dosage	Wt
CHS7084L-2	71	110 (Pump)	Φ50	0.2 ml	71.4g(Pump)

Unlimited clean beauty potentials, EBM AIRLESS BOTTLES.



sales@srpackaging.com